



HIGH SPEED STEELS

Available Product Variants

Long Products*	Plates
----------------	--------

Product Description

BÖHLER \$393 MICROCLEAN - "Standardized"

This grade complies with the ASTM A600 AISI T15 material standard. With MICROCLEAN technology, this material shows excellent reliability in many cutting and cold-work applications.

Process Melting

Powder metallurgy

Properties

- > Toughness & Ductility: high
- > Wear Resistance : high
- > Compressive strength: very high
- > Edge Stability : very high
- > Grindability: high
- > Hot Hardness (red hardness) : very high

Applications

- > Broaches and Reamers
- > Fine Blanking, Stamping, Blanking
- > Rolling
- > Twist Drills and Taps

- > Cold Forming / Coining
- > Gear Cutting, Shaving and Shaping Tools
- > Shearing / Machine Knives

- > End Mills
- > Powder Pressing
- > Wear parts

Technical data

Material designation		Standards	
AISI: T15	AISI	A600	ASTM

Chemical composition (wt. %)

С	Cr	V	W	Со
1.63	4.0	4.75	12.10	5.0



^{*)} Presented data refer exclusivly to long products. Please observe the detailed explanations at the end of the data sheet (pdf).





Material characteristics

	Compressive strength	Grindability	Red hardness	Toughness	Wear resistance	Edge Stability
BÖHLER S290	****	*	****	**	****	***
BÖHLER S390	***	***	****	***	***	***
BÖHLER S590	***	***	****	***	***	***
BÖHLER S690	***	***	**	****	***	**
BÖHLER S790	***	***	**	***	**	***
BÖHLER S793	***	***	****	***	***	***

Delivery condition

An			

Aimeaica	
Hardness (HB) max. 300 drawn execution max. 320 HB	
Tensile Strength (N/mm² ksi) max. 1,080 157	

Heat treatment

Ar	-	_	_		
Αľ	าท	$\boldsymbol{\epsilon}$	a	ш	10

		4 h controlled slow cooling in furnace (10 - 20°C / (50 - 68°F) to 550°C / 2 h (1022°F / 2 h) cooling in furnace.
--	--	--

Stress relieving

		Slow cooling furnace. To relieve stresses set up by extensive machining or in tools of intricate shape. After through heating, hold in neutral atmosphere for 1 to 2 hours.
--	--	---

Hardening and Tempering


Temperature	1,180 to 1,240 °C 2,156 to 2,264 °F	Salt bath, vacuum Preheating: 1st stage \sim 500 °C, 2nd stage \sim 850 °C, 3rd stage \sim 1050 °C Austenitising: 1180 - 1240 °C, holding time after complete heating 80 seconds, maximum 150 seconds, to avoid material damage due to overheating. Quenching: oil, warm bath (500 - 550 °C), gas
Temperature	540 to 570 °C 1,004 to 1,058 °F	Slow heating to tempering temperature immediately after austenitising. Dwell time in the furnace 1 hour per 20 mm material thickness (at least 1 hour) Slow cooling to room temperature between each tempering step 3 tempering cycles recommended Hardness see tempering chart







Tempering Chart



Holding time 3 x 2 hours Specimen size: square 25 mm

Physical Properties

Temperature (°C °F)	20 68
Density (kg/dm³ Ib/in³)	8.19 0.3
Thermal conductivity (W/(m.K) BTU/ft h °F)	-
Specific heat (kJ/kg K BTU/lb °F)	-
Spec. electrical resistance (Ohm.mm²/m 10 ⁻⁴ Ohm.inch²/ft)	-
Modulus of elasticity (10 ³ N/mm ² 10 ³ ksi)	218 31.62

Long Products: For additional specifications and technical requirements, please contact our regional voestalpine BÖHLER sales companies.

Open Die Forgings: Product Variant may differ in terms of melting process, technical data, delivery, and surface condition as well as available product dimensions. Please contact the business unit Open Die Forgings of voestalpine BÖHLER Edelstahl GmbH & Co KG.

Sheet & Plates: Product Variant may differ in terms of melting process, technical data, delivery, and surface condition as well as available product dimensions. Please contact voestalpine BÖHLER Bleche GmbH & Co KG.

The data contained in this brochure is merely for general information and therefore shall not be binding on the company. We may be bound only through a contract explicitly stipulating such data as binding. Measurement data are laboratory values and can deviate from practical analyses. The manufacture of our products does not involve the use of substances detrimental to health or to the ozone layer.

voestalpine BÖHLER Edelstahl GmbH & Co KG

Mariazeller Straße 25 8605 Kapfenberg, AT T. +43/50304/20-0 E. info@bohler-edelstahl.at https://www.voestalpine.com/bohler-edelstahl/de/

